



### LED Power PEN 2.0

UV LED point source

Max. irradiation intensity: 16.000 mW/cm<sup>2</sup>

Wavelength: 365, 405 nm

Air cooled

### System-Features

- less heat impact
- no start up phase
- no standby-mode required

### Advantages

- optimum adhesive curing performance
- suitable for heat sensitive materials
- low electrical power input
- focussed irradiation characteristic

## LED Power Pen 2.0

The LED Power Pen is an LED-technology based reliable point source with an output spectrum of 365/405 nm +/- 10 nm.

### Advantages of LED-technology

The use of LED devices offers the following advantages: LED's do not emit IR radiation. With reduced heat output the processing of almost all heat sensitive materials is possible. The monochromatic spectrum of the LED Power Pen matches the absorption of photoinitiators in UV curable adhesives and allows a fast and efficient cure.

The LED Power Pen can be switched on and off as often as necessary. He does not require a warm-up or cooling phase.

### Applications

The Power Pen is suitable for a large range of applications:

- Bonding and fixing of components in the electronic, medical and optical industry
- Fluorescent excitation for material testing and image processing
- High-intensity UV irradiation for biological, chemical and pharmaceutical purposes

### Flexible use

Due to its compact size and low weight the LED Power Pen can be used in difficult accesable areas. The LED Power Pen is powered via an external plug-in supply unit (adaptable for the world wide use) which is included in the scope of delivery. The LED Power Pen is manually operated by using a pressure switch on the unit.

Optionally, the LED Power Pen is available with a control box for external activation (e.g. foot switch) or for activation via a potential-free PLC input signal.

Additionally, the control box provides an output signal for operation monitoring.



Control unit LED Power Pen (option)

### High process security

The LED Power Pen has an internal power control and a temperature switch to protect the unit.

### Technical Data

Peak wavelength	365/405 nm +/- 10 nm
UVA Intensity in 12 mm distance*	10.000 mW/cm <sup>2</sup> at 365 nm 16.000 mW/cm <sup>2</sup> at 405 nm
Electrical power input	ca. 5 W
Mains supply	From external net 100-240V AC
Dimensions (Ø x length)	26 mm x 140,5 mm
Weight	140 g
Continuous operation without additional cooling	max. 10 minutes

\* measured with Höhle UV-Meter and LED sensor



Dr. Höhle AG UV Technology, Lochhamer Schlag 1, 82166 Gräfelfing/München, Germany  
Phone: +49 89 85608-0, Fax: +49 89 85608-148, [www.hoenle.de](http://www.hoenle.de)

Operating parameters depend on production characteristics and may differ from the foregoing information. We reserve the right to modify technical data. © Copyright Dr. Höhle AG. Updated 05/16.

